

**WK K PH2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)**Utbytesklingor till vridmomentsskruvmejsel**

Klingprofil enligt DIN 5260-PH, ISO 8764/1-PH

**Allmänna beställningsdata**

Typ	WK K PH2
Art.nr.	<a href="#">9918590000</a>
Artikelbeteckning	Skruvmejselinsats, 175 mm, 2
GTIN (EAN)	4032248388967
Frp	1 Stück

## WK K PH2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Tekniska data

## Mått och vikter

Bredd	175 mm	Byggbredd (tum)	6,89 inch
Höjd	4 mm	Bygghöjd (tum)	0,157 inch
Djup	4 mm	Byggdjup (tum)	0,157 inch
vikt	22 g	Nettovikt	22 g

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Skruvverktyg

Form	Crosshead	Klinglängd	175 mm
Klingmått krysspår	2	storlek	2

## Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC002115
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

## Godkännanden

Godkännanden



## Downloads

Broschyr/Katalog [CAT 3 HDC 17/18 EN](#)  
[CAT 6 TOOLS 15/16 EN](#)  
[CAT 5 ENCL 17/18 EN](#)