

WK K PZO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Utbytesklingor till vridmomentsskruvmejsel**

Klingprofil enligt DIN 5260-PZ, ISO 8764/1-PZ

Allmänna beställningsdata

Typ	WK K PZO
Art.nr.	991860000
Artikelbeteckning	Skruvmejselinsats, 175 mm
GTIN (EAN)	4032248388974
Frp	1 Stück

WK K PZO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data

Mått och vikter

Bredd	175 mm	Byggbredd (tum)	6,89 inch
Höjd	4 mm	Bygghöjd (tum)	0,157 inch
Djup	4 mm	Byggdjup (tum)	0,157 inch
vikt	21 g	Nettovikt	25 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Form	Pozidrive	Klinglängd	175 mm
storlek	0		

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC002115
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

Godkännanden

Godkännanden



Downloads

Broschyr/Katalog [CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)