

**Industriellt Ethernet
IE-PIC-HYB-S-0,75-300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Hybrid 10pol. Insatser för stickkontakter var.1 /4 /5 /14

Allmänna beställningsdata

Typ	IE-PIC-HYB-S-0,75-300
Art.nr.	1068950000
Artikelbeteckning	Crimpkontakt, Stickkontakt, Hybrid
GTIN (EAN)	4032248823109
Frp	300 Stück

**Industriellt Ethernet
IE-PIC-HYB-S-0,75-300**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data**Mått och vikter**

Nettovikt 0,27 g

Temperaturer

Drifttemperatur _____ Lagertemperatur _____
Installation temperature _____

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Allmänna data

Ledardiameter, fintrådig, min. 0,75 mm² Ledardiameter, fintrådig, max. 0,75 mm²

Elektriska egenskaper

Märkspänning 24 V

Klassificeringar

ETIM 4.0	EC001264	ETIM 5.0	EC001264
ETIM 6.0	EC001121	eClass 6.2	27-25-05-04
eClass 7.1	27-25-05-04	eClass 8.1	19-17-01-25
eClass 9.0	27-44-03-90	eClass 9.1	27-44-09-90

Godkännanden

Godkännanden



ROHS Uppfyllelse

Downloads

Användardokumentation [MAN IE GUIDE DE](#)
[MAN IE GUIDE EN](#)
Broschyr/Katalog [CAT 9 IETH 15/16 EN](#)
[FL FIELDWIRING EN](#)
[PI PROFINET CABLING EN](#)

Industriellt Ethernet IE-PIC-HYB-S-0,75-300

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Ritningar

Profilritning

