

**Industriellt Ethernet  
IE-BIC-HYB-P-0,5-300**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Hybrid 10pol. Insatser för stickkontakter var.1 /4 /5 /14

**Allmänna beställningsdata**

Typ	IE-BIC-HYB-P-0,5-300
Art.nr.	<a href="#">1096150000</a>
Artikelbeteckning	Crimpkontakt, Fläns, Hybrid
GTIN (EAN)	4032248869114
Frp	300 Stück

**Industriellt Ethernet  
IE-BIC-HYB-P-0,5-300**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Tekniska data****Mått och vikter**

Nettovikt	0,29 g
-----------	--------

**Temperaturer**

Drifttemperatur	Lagertemperatur
Installation temperature	

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Allmänna data**

Ledardiameter, fintrådig, min.	0,2 mm <sup>2</sup>	Ledardiameter, fintrådig, max.	0,5 mm <sup>2</sup>
--------------------------------	---------------------	--------------------------------	---------------------

**Elektriska egenskaper**

Märkspänning	24 V
--------------	------

**Klassificeringar**

ETIM 3.0	EC000018	ETIM 4.0	EC000018
ETIM 5.0	EC000018	ETIM 6.0	EC001121
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-09-90		

**Godkännanden**

ROHS	Uppfyllelse
------	-------------

**Downloads**

Användardokumentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Broschyr/Katalog	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**Industriellt Ethernet  
IE-BIC-HYB-P-0,5-300**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Ritningar****Profilritning**