

**Industriellt Ethernet
IE-PS-V04P-2LC-SM-BP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



PushPull stickkontaktsats enligt IEC 61076-3-106 var.4
(IEC24702) i plast, inkl. LC-insats

Allmänna beställningsdata

Typ	IE-PS-V04P-2LC-SM-BP
Art.nr.	1963350000
Artikelbeteckning	Kontaktidon fiber, Variant 4, LC-Duplex Singlemode, böjskydd, IP67
GTIN (EAN)	4032248651825
Frp	10 Stück

**Industriellt Ethernet
IE-PS-V04P-2LC-SM-BP**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Nettovikt	43,1 g
-----------	--------

Temperaturer

Driftstemperatur, max	70 °C	Driftstemperatur, min.	-40 °C
Drifttemperatur	-40 °C...70 °C	Lagertemperatur	
Installation temperature			

Allmänna data

Anslutning 1	LC	Anslutning 2	limning, kontaktpressning, polering
Artikelbeskrivning	Variant 4, LC-Duplex Singlemode, böjskydd	Dämpning	0,5 dB Singlemode, 0,4 dB Multimode
Fibertyp	Singlemode	Färgkod	övriga
Kapslingsmaterial	PA UL 94 V0	Kapslingsmaterial insats	PBT, Zinkpressgjutning
Manteldiameter, max.	10 mm	Manteldiameter, min.	5 mm
Skyddsklass	IP67	Stickcykler	500
Återflödesdämpning	40 dB Singlemode; 30 dB Multimode		

Normer

Kontaktton Norm	IEC 61076-3-106 var. 4, IEC 61754-20
-----------------	---

Klassificeringar

ETIM 3.0	EC001121	ETIM 4.0	EC002641
ETIM 5.0	EC002641	ETIM 6.0	EC001122
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-08
eClass 6.2	27-26-07-08	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-22
eClass 9.1	19-07-01-22		

Godkännanden

Godkännanden



ROHS	Uppfyllelse
------	-------------

Downloads

Användardokumentation	MAN IE GUIDE DE MAN IE GUIDE EN
Broschyr/Katalog	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Godkännande/Certifikat/Dokument om överensstämmelse	GOST Approval
Teknikuppgifter	WSCAD

Datablad**Industriellt Ethernet
IE-PS-V04P-2LC-SM-BP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar**Profilritning**