

**Industriellt Ethernet  
IE-PS-V04P-2SC-POF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



PushPull stickkontaktsats enligt IEC 61076-3-106 var.4  
(IEC24702) i plast, inkl. SC-insats

**Allmänna beställningsdata**

Typ	IE-PS-V04P-2SC-POF
Art.nr.	<a href="#">1963380000</a>
Artikelbeteckning	Kontaktidon fiber, Version 4, SC-RJ POF, IP67
GTIN (EAN)	4032248651856
Frp	10 Stück

**Industriellt Ethernet  
IE-PS-V04P-2SC-POF**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Tekniska data****Mått och vikter**

Nettovikt	48,7 g
-----------	--------

**Temperaturer**

Driftstemperatur, max	70 °C	Driftstemperatur, min.	-40 °C
Drifttemperatur	-40 °C...70 °C	Lagertemperatur	
Installation temperature			

**Allmänna data**

Anslutning 1	SCRJ	Anslutning 2	Snabb anslutningsteknik; kontaktpressning, kapning
Artikelbeskrivning	Version 4, SC-RJ POF	Dämpning	0,5 dB Singlemode, 0,4 dB Multimode, ≤ 1,0 dB POF
Fibertyp	POF	Färgkod	övriga
Kapslingsmaterial	PA UL 94 V0	Kapslingsmaterial insats	PA, Zinkpressgjutning
Manteldiameter, max.	10 mm	Manteldiameter, min.	5 mm
Skyddsklass	IP67	Stickcykler	500
Återflödesdämpning	40 dB Singlemode; 30 dB Multimode		

**Normer**

Kontaktton Norm	IEC 61076-3-106 var. 4, IEC 61754-24
-----------------	---

**Klassificeringar**

ETIM 3.0	EC001121	ETIM 4.0	EC002641
ETIM 5.0	EC002641	ETIM 6.0	EC001122
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-08
eClass 6.2	27-26-07-08	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-22
eClass 9.1	19-07-01-22		

**Godkännanden**

Godkännanden



ROHS	Uppfyllelse
------	-------------

**Downloads**

Användardokumentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Broschyr/Katalog	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Godkännande/Certifikat/Dokument om överensstämmelse	<a href="#">GOST Approval</a>
Teknikuppgifter	<a href="#">WSCAD</a>

**Datablad****Industriellt Ethernet  
IE-PS-V04P-2SC-POF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Ritningar****Profilritning**