

**Industriellt Ethernet  
IE-BS-V05M-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



HDC stickkontaktsats enligt IEC 61076-3-106 var.5 i  
plast metall inkl. RJ45-insats

**Allmänna beställningsdata**

Typ	IE-BS-V05M-RJ45-C
Art.nr.	<a href="#">1963510000</a>
Artikelbeteckning	Fläns RJ45, IP67, Variant 5, Koppling, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)
GTIN (EAN)	4032248645602
Frp	10 Stück

**Industriellt Ethernet  
IE-BS-V05M-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Tekniska data****Mått och vikter**

Nettovikt	61,3 g
-----------	--------

**Temperaturer**

Driftstemperatur, max	70 °C	Driftstemperatur, min.	-40 °C
Drifttemperatur	-40 °C...70 °C	Lagertemperatur	
Installation temperature			

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Allmänna data**

Anslutning 1	RJ45	Anslutning 2	RJ45
Artikelbeskrivning	Variant 5, Koppling	Tätningmaterial	NBR
Kapslingsmaterial	Aluminiumpressgjutgods	Kategori	Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)
Kontaktyta	Guld över nickel	Avskärmning	360° runtom slutet
Skyddsklass	IP67	Stickcykler	750

**Normer**

Kontaktton Norm	IEC 61076-3-106 var. 5, IEC 60603-7-5 1	Certifikat-Nr. (cULus)	E316369
-----------------	--	------------------------	---------

**Klassificeringar**

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC001121
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-44-03-90
eClass 9.1	27-44-03-90		

**Godkännanden**

Godkännanden



ROHS	Uppfyllelse
------	-------------

**Industriellt Ethernet  
IE-BS-V05M-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Tekniska data****Downloads**

Användardokumentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Broschyr/Katalog	<a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">MB FREECONTACT EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Godkännande/Certifikat/Dokument om överensstämmelse	<a href="#">GOST Approval</a> <a href="#">DUXR.E316369</a> <a href="#">PROFINET Manufacturer's Declaration</a>
Teknikuppgifter	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>

**Datablad****Industriellt Ethernet  
IE-BS-V05M-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Ritningar****Profilritning**