

**RIDERSERIES RCM
SCM-I CLIP M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Produktillustration

Låsbygel i metall till reläer i RIDERSERIES RCM.

Allmänna beställningsdata

Typ	SCM-I CLIP M
Art.nr.	8869450000
Artikelbeteckning	RIDERSERIES RCM, Låsbygel
GTIN (EAN)	4032248614301
Frp	10 Stück

**RIDERSERIES RCM
SCM-I CLIP M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data**Mått och vikter**

Nettovikt	0,559 g
-----------	---------

Temperaturer

Driftstemperatur, max	70 °C	Driftstemperatur, min.	-40 °C
Fuktighet	40 °C/93 % rel. fuktighet, ingen kondens	Lagertemperatur, max.	85 °C
Lagertemperatur, min.	-40 °C	Drifttemperatur	-40 °C...70 °C
Lagertemperatur	-40 °C...85 °C		

Allmänna uppgifter

Material	Metall	Färgkod	Silver
----------	--------	---------	--------

Klassificeringar

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

Godkännanden

Godkännanden



ROHS	Uppfyllelse
------	-------------

Downloads

Broschyr/Katalog	CAT 4.2 ELECTR 18/19 EN
Teknikuppgifter	EPLAN.WSCAD
Teknikuppgifter Data	STEP