

**Montageskenor
TS 27X12.5M/ST/F.ZN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Produktillustration**Allmänna beställningsdata**

Typ	TS 27X12.5M/ST/F.ZN
Art.nr.	1802690000
Artikelbeteckning	Montageskenor, Montageskena, DIN EN 60715, Stål
GTIN (EAN)	4032248257201
Frp	2 m

**Montageskenor
TS 27X12.5M/ST/F.ZN**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data**Mått och vikter**

Bredd	27 mm	Byggbredd (tum)	1,063 inch
Höjd	12,5 mm	Bygghöjd (tum)	0,492 inch
Djup	12,5 mm	Byggdjup (tum)	0,492 inch
Nettovikt	50 g		

Montageskena

Tjocklek	2 mm
----------	------

Klassificeringar

ETIM 3.0	EC001285	ETIM 4.0	EC001285
ETIM 5.0	EC001285	ETIM 6.0	EC001285
UNSPSC	30-21-18-01	eClass 5.1	27-14-06-04
eClass 6.2	27-14-11-43	eClass 7.1	27-14-11-43
eClass 8.1	27-14-11-43	eClass 9.0	27-40-06-02
eClass 9.1	27-40-06-02		

Godkännanden

ROHS	Uppfyllelse
------	-------------

Downloads

Användardokumentation	StorageConditionsTerminalBlocks
Broschyr/Katalog	CAT 1 TERM 16/17 EN
Teknikuppgifter	EPLAN, WSCAD
Teknikuppgifter Data	STEP