

**Klippon EBi FS (Essential Box industrial - Fixing Screw)
KEBI FS 604022 S2B1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The Klippon® EBi industrial enclosure series protects your components reliably if they are used in moderate environmental conditions and is designed for everyday applications. With the ever-increasing need for individual application solutions, the Klippon® EBi with its high degree of protection and impact resistance is ideally suited to your needs. Our standard product is the Klippon® EBi QL – with hinged door and double-bit key lock. A variant with mounting screws is also available, but is only manufactured on request and is subject to a minimum order quantity. DNV GL and cULus approvals are also available on request.

Allmänna beställningsdata

Typ	KEBI FS 604022 S2B1
Art.nr.	2471100000
Artikelbeteckning	Klippon EBi FS (Essential Box industrial - Fixing Screw), Tom kapsling, Rostfria stål kapslingar, Höjd: 600 mm, Bredd: 400 mm, Djup: 220 mm, Flänsplattor: nedre, Material: Rostfritt stål 1.4301 (304), borstad, Silver
GTIN (EAN)	4050118591361
Frp	1 Stück

Klippon EBi FS (Essential Box industrial - Fixing Screw)

KEBI FS 604022 S2B1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data

Mått och vikter

Bredd	400 mm	Byggbredd (tum)	15,748 inch
Höjd	600 mm	Bygghöjd (tum)	23,622 inch
Djup	220 mm	Byggdjup (tum)	8,661 inch
Montagemått bredd	350 mm	Montagemått höjd	550 mm
Vägg tjocklek, max.	2 mm	Vägg tjocklek, min.	2 mm
Nettovikt	12 700 000 g	Diameter	9 mm

Allmänna uppgifter

Användningsområden	Hamnanläggningar, Maskintillverkning, Transportväsende, Fartygsbyggnad, Förpackningsindustri, Processindustri	Flänsplattor	nedre
Materialtjocklek	1,5 mm	Materialtjocklek fläns	1,5 mm
Materialtjocklek kapsling	1,5 mm	Materialtjocklek lock	1,5 mm
Montering av flänsplatta	M5 Torxskruv i rostfritt stål TX20	Monteringsanvisning	Svetsad montagevinkel, Montageplatta
Normer	DIN EN 62208, IEC 60529	Tätningmaterial för flänsplatta	EPDM
Tätningmaterial för lock	Skummad PUR	Vridmoment för lockskrivar	2,5 Nm
Material	Rostfritt stål 1.4301 (304)	Tätningmaterial	Skummad PUR, EPDM
Yta	borstad	Drifttemperatur, min.	-40 °C
Drifttemperatur, max	85 °C	Slagtålighet	10.00 J
Skyddsklass	IP66	Kapslingens fastsättning	Fästörön, Installation genom kapslingens bakvägg
Fastsättning av lock	M6 torx stainless steel screws with slot, avtagbart lock + M6-skrivar	Komponentfastsättning	skruvad

Certifikatnummer kapsling

Certifikat-Nr. (cULus) E256877

Jordning kapsling

Jordning, kapsling, extern	M6 jordtapp	Jordning, kapsling, intern	Påsvetsad M6 jordskriv i rostfritt stål i kapslingsunderdel och lock.
Jordning, kapsling, lock	Påsvetsad M6 jordskriv i rostfritt stål i kapslingsunderdel och lock.		

Klassificeringar

ETIM 6.0	EC000261	eClass 6.2	27-14-91-07
eClass 9.0	27-18-01-01	eClass 9.1	27-18-92-90

Produktinformation

Produktinformation Minimum order quantity (50 pieces)

Datablad**Klippon EBi FS (Essential Box industrial - Fixing Screw)
KEBI FS 604022 S2B1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Tekniska data**Godkännanden**

Godkännanden



ROHS

Uppfyllelse

