

**Cabtite (kabelinföringssystem)
CABTITE FR 10/6 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

Allmänna beställningsdata

Typ	CABTITE FR 10/6 BK
Art.nr.	2583480000
Artikelbeteckning	Ram, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvart, Höjd: 19.6 mm, Bredd: 70 mm, Djup: 19.6 mm, -40 °C...120 °C, IP54, IP65, IP66
GTIN (EAN)	4050118616873
Frp	1 Stük

Cabtite (kabelinföringssystem)
CABTITE FR 10/6 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data**Mått och vikter**

Längd	106 mm	Bygglängd (tum)	4,173 inch
Bredd	70 mm	Byggbredd (tum)	2,756 inch
Höjd	19,6 mm	Bygghöjd (tum)	0,772 inch
Höjd lägstbyggande	19,6 mm	Djup	19,6 mm
Byggdjup (tum)	0,772 inch	Montagemått bredd	32 mm
Montagemått höjd	83 mm	Nettovikt	0,07 g
Diameter	5,5 mm		

Allmän information

Åtdragningsmoment	3 Nm	Öppningsbredd	46 mm
Öppningslängd	68,5 mm	Brännbarhetsklass enligt UL 94	V-0
Tätningselement	6 små tätningar eller 1 stor tätning plus 2 små tätningar	Halogener	Nej
Silikon	Nej	Tätning	TPE
Material	Polyamid, glasfiberförstärkt		

Klassificeringar

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Godkännanden

Godkännanden



ROHS

Uppfyllelse

Downloads

Användardokumentation	Cabtite Installation Instructions
Teknikuppgifter Data	STEP

Cabtite (kabelinföringssystem) CABTITE FR 10/6 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Ritningar

