

**Cabtite (kabelinföringssystem)
CABTITE CR 24/10 EMV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The Cabtite cable entry system offers maximum flexibility in the cable management of control cabinets, enclosures and machines, while at the same time saving time, as well as providing secure sealing and strain relief for pre-terminated and non-terminated cables. Cabtite's modular design of frame, grid inlays and sealing elements enables rapid configuration of cut-outs for pre-terminated cables - without the use of tools and with a reliable sealing of IP66 according to DIN EN 60529. Frame. Inlay. Sealing element. Three basic components in the modular system guarantee highest flexibility, variability and diversity of variants.

Allmänna beställningsdata

Typ	CABTITE CR 24/10 EMV
Art.nr.	2583890000
Artikelbeteckning	Kabelskyddsskivor, Cabtite (kabelinföringssystem), Stål förzinkat, Silver, Höjd: 16 mm, Bredd: 35.23 mm, Djup: 16 mm
GTIN (EAN)	4050118647068
Frp	10 Stück

**Cabtite (kabelinföringssystem)
CABTITE CR 24/10 EMV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data**Mått och vikter**

Längd	140 mm	Bygglängd (tum)	5,512 inch
Bredd	35,23 mm	Byggbredd (tum)	1,387 inch
Höjd	16 mm	Bygghöjd (tum)	0,63 inch
Djup	16 mm	Byggdjup (tum)	0,63 inch
Montagemått bredd	5,3 mm	Montagemått höjd	5,91 mm
Nettovikt	46,96 g	Diameter	5,3 mm

Allmän information

Halogener	Nej	Silikon	Nej
Material	Stål förzinkat		

Klassificeringar

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

Godkännanden

ROHS	Uppfyllelse
------	-------------

Downloads

Teknikuppgifter Data	STEP
----------------------	----------------------