

EMC cabinet IP40 HxWxD=2000x 900x 800



Figure similar

Versiyon

ürün marka adı	SIVACON
ürün tanımı	EMU dolap
kurulum türü	tek başına monte
yüzey modeli	toz kaplama
ürün modeli / EMU modeli	Evet
anahtar dolabı modeli / PC modeli	Hayır
anahtar dolabı modeli / panel modeli	Hayır

Koruma sınıfı

IP koruma türü	IP40
montaj uygunluğu	
• inç ebat için	10 inç, 17 inç, 19 inç, 21 inç, 23 inç, 24 inç
• metrik ebat için	M8
kullanma uygunluğu / harici kullanım için	Hayır

Görünüm

RAL renk numarası	RAL 7032
renk	çakıl grisi

ürün bileşeni	
• çıkarılabilir çerçeve	Hayır
• havalandırma kapısı	Hayır
• montaj plakası	Hayır
• arka kapı	Hayır
• eğik tavan	Hayır
• camlı kapı	Hayır
• derinliği ayarlanabilir montaj plakası	Hayır
kilit sayısı	1
kapı sayısı	1

Mekanik Tasarım

yükseklik	2 000 mm
genişlik	900 mm
derinlik	800 mm
yükseklik ayırma birimi sayısı / montaj yüksekliği için	38
sabitlenme türü	dik duruş
sabitlenme türü / montaj 19 inç	Evet
net ağırlık	155 kg
malzeme	çelik

Sertifikalar

referans işareti			
• DIN EN 61346-2 uyarınca		U	
General Product Approval	Declaration of Conformity	other	



[Miscellaneous](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=8MF5098-4ES>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/8MF5098-4ES>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF5098-4ES

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>