

NEOZED, fuse base, D02, 1-pole, 63 A, Un AC: 400 V, Un DC: 250 V



Figure similar

### Versiyon

ürün marka adı	NEOZED
ürün tanımı	Emniyet soketi
ürün modeli	NEOZED montaj emniyet kaidesi

### Genel teknik veriler

kutup sayısı	1
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	D02

### Besleme gerilimi

işletim gerilimi / anma değeri	400 V
--------------------------------	-------

### Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	1 W
--	-----

### Ana devre

işletim akımı / anma değeri	63 A
-----------------------------	------

### Ürün Detayı

ürün bileşeni / kapak	Evet
-----------------------	------

### Mekanik Tasarım

yükseklik	59 mm
genişlik	26,8 mm
derinlik	41 mm
sabitlenme türü	DIN rayı
net ağırlık	92 g
malzeme / D emniyet duygusu	Porselen

### Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

### Diğer bilgiler

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG1653>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG1653>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG1653](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1653)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

