

NEOZED, fuse base, D01, 3-pole, 16 A, Un AC: 400 V, Un DC: 250 V



Figure similar

Versiyon	
ürün marka adı	NEOZED
ürün tanımı	Emniyet soketi
ürün modeli	NEOZED montaj emniyet kaidesi
Genel teknik veriler	
kutup sayısı	3
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	D01
Besleme gerilimi	
işletim gerilimi / anma değeri	400 V
Dağıtma	
Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	0,6 W
Ana devre	
işletim akımı / anma değeri	16 A
Ürün Detayı	

ürün bileşeni / kapak	Evet
-----------------------	------

Mekanik Tasarım

yükseklik	54 mm
genişlik	80,8 mm
derinlik	40 mm
sabitlenme türü	DIN rayı
net ağırlık	216 g
malzeme / D emniyet duygusu	Porselen

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

General Product Approval

Declaration of Conformity



Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG5553>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG5553>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG5553

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

