

SITOR cylindrical fuse link, 10 x 38 mm, 20 A, aR, Un AC: 600 V, Un DC: 700 V, DC according to UL



Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR silindirik sigorta buşonu
ürün modeli	DC UL uyarınca

Genel teknik veriler

sigorta soketinin çalışma sınıfı	aR
sigorta soketinin büyüklüğü	10x38 mm
gerilim türü	AC
akım / AC'de / anma değeri	20 A
besleme gerilimi / DC'de	700 V
işletim gerilimi / anma değeri	600 V

Dağıtım

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	4,8 W
--	-------

Ana devre

işletim akımı / nominal değer	20 A
-------------------------------	------

Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
---------------------------------	-------

montaj pozisyonu	isteğe bağı, tercihen dikey
net ağırlık	16 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

Declaration of Conformity



[Miscellaneous](#)



Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NC1020>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NC1020>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1020

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



