

SETRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 32 A, Un AC: 690 V, for busbar system 8US 60 mm



Versiyon

ürün marka adı	SETRON
ürün tanımı	Silindirik sigorta tutucusu
ürün modeli	8US 60 mm elektrik dağıtım rayı sistemi için

Genel teknik veriler

kutup sayısı	3
sigorta elemanı ebadı	10x38 mm

Besleme gerilimi

akım / AC'de / anma değeri	32 A
işletim gerilimi	
• AC'de / anma değeri	690 V
IP koruma türü	IP20

Mekanik Tasarım

yükseklik	200 mm
genişlik	27 mm
derinlik	79 mm

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

Declaration of Conformity



CSA



UR



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW7431>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW7431>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7431

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





