

SITOR cylindrical fuse link, 14x51 mm, 20 A, aR, Un AC: 690 V, Un DC: 600 V, DC according to UL, Striker indicator



Versiyon	
ürün marka adı	SETRON
ürün tanımı	SITOR silindirik sigorta buşonu
ürün modeli	DC UL uyarınca
gösterge sensörü modeli	Vurma çubuğu-bildirim elemanı

  

Genel teknik veriler	
sigorta soketinin çalışma sınıfı	aR
sigorta soketinin büyüklüğü	14x51 mm
gerilim türü	AC
akım / AC'de / anma değeri	20 A
besleme gerilimi / DC'de	600 V
işletim gerilimi / anma değeri	690 V

  

Dağıtma	
Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	6 W

  

Ana devre	
işletim akımı / nominal değer	20 A

  

Ürün Detayı	
-------------	--

ürün bileşeni / darbe dedektörü	Evet
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	19 g

## Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

### General Product Approval

### Declaration of Conformity



UR

[Miscellaneous](#)



EG-Konf.

## Diğer bilgiler

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NC1420-5>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NC1420-5>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC1420-5](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1420-5)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



