

SITOR cylindrical fuse link, 22x58 mm, 40 A, aR, Un AC: 690 V, Un DC: 700 V, DC according to UL



### Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR silindirik sigorta buşonu
ürün modeli	DC UL uyarınca

### Genel teknik veriler

sigorta soketinin çalışma sınıfı	aR
sigorta soketinin büyüklüğü	22x58 mm
gerilim türü	AC
akım / AC'de / anma değeri	40 A
besleme gerilimi / DC'de	700 V
işletim gerilimi / anma değeri	690 V

### Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	8,5 W
--	-------

### Ana devre

işletim akımı / nominal değer	40 A
-------------------------------	------

### Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
---------------------------------	-------

montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	56 g

## Sertifikalar

### referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

### General Product Approval

### Declaration of Conformity



[Miscellaneous](#)



## Diğer bilgiler

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NC2240>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NC2240>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC2240](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2240)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



