

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 1, H:  
1950 mm, W: 300 mm, T: 250 mm, RAL 7035



### Versiyon

ürün marka adı	ALPHA 630
ürün tanımı	Ayaklı pano
yüzey işleme	toz kaplamalı

### Koruma sınıfı

IP koruma türü	IP55
etkileşim uygunluğu / flaş koruması	Evet
kullanma uygunluğu / harici kullanım için	Hayır

### Görünüm

RAL renk numarası	RAL 7035
ürün bileşeni	
• kablo girişi	Evet
• montaj plakası	Hayır
ürün ilavesi / opsiyonel / yan yana seri bağlantı	Evet

### Mekanik Tasarım

yükseklik	1 950 mm
genişlik	300 mm
derinlik	250 mm

montaj derinliđi	250 mm
net ađırlık	30 kg
malzeme / mahfaza	Çelik

## Sertifkalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



VDE

[Miscellaneous](#)



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

## other

[Miscellaneous](#)

## Diđer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=8GK1323-8KN13>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/8GK1323-8KN13>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KN13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KN13)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



