

SITOR fuse link, with slotted blade contacts, NH3, In: 355 A, gR, Un AC: 1000 V, Un DC: 440 V, front indicator



Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR sigorta buşonu
ürün modeli	Yarıklı bıçaklı kontaklar ile
gösterge sensörü modeli	Ön gösterge
anahtar kontak modeli	korozyona dayanıklı, gümüş kaplamalı

Genel teknik veriler

sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	NH3
sigorta soketinin çalışma sınıfı	gR

Besleme gerilimi

gerilim türü	AC/DC
akım / AC'de / anma değeri	355 A
besleme gerilimi	
• AC'de / anma değeri	1 000 V
• DC'de	440 V

Anahtarlama kapasitesi

anahtarlama akım durumu	
• IEC 60947-2 uyarınca / anma değeri	100 kA

Ürün Detayı

ürün açıklaması Karıştırma yok

Mekanik Tasarım

montaj pozisyonu isteğe bağlı, tercihen dikey

Çevresel koşullar

ortam sıcaklığı -20 ... +50 °C

Çevre kategorisi % 95 bağıl nemde -20 ila +50

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

Declaration of Conformity

other

[Miscellaneous](#)



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NE3434-3C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NE3434-3C>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE3434-3C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

