

auxiliary current switch, Central half module



Versiyon

ürün marka adı	SETRON
ürün tanımı	Uzaktan şalter
darbe akım anahtarı modeli	Merkezi kumanda için mekanik

Genel teknik veriler

impuls süresi / minimum	50 ms
potansiyel ayırım / mıknatıs ve kontak arasında	Evet
anahtarlama gerilimi / kontaklar / AC'de / minimum	10 V
anahtarlama akımı / AC'de / kontak başına / minimum	100 mA

Besleme gerilimi

gerilim türü	AC
--------------	----

Koruma sınıfı

IP koruma türü	IP20
----------------	------

Anahtarlama kapasitesi

anahtarlama akım durumu	16 A
• cos phi 0,6'da	

Ürün fonksiyonu

ürün fonksiyonu / doğrudan kullanım	Evet
-------------------------------------	------

Numara

açıcı sayısı	0
kapayıcı sayısı	0
değiştirici sayısı	0

Mekanik Tasarım

yükseklik	90 mm
genişlik	9 mm
açıklık genişliği / kontaklar	1,2 mm
derinlik	73 mm
montaj yüksekliği	90 mm
montaj derinliği	73 mm
en birimi sayısı	0,5
sabitleme türü	DIN rayı
montaj pozisyonu	yatay ve dikey
net ağırlık	45 g

Çevresel koşullar

ortam sıcaklığı	-25 ... +70 °C
-----------------	----------------

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	K
• IEC 81346-2:2009 uyarınca	K

Declaration of Conformity



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5TT4931>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5TT4931>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT4931

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



