

INSTA contactor 0/1-automatic with 2 NO contacts Contact for 230 V AC, 400V 20A Control AC/24 V DC



Versiyon

ürün marka adı	SETRON
ürün tanımı	Insta kontaktörler
gerilim türü / işletim gerilimi	AC
gerilim türü / çalıştırmak için	AC/DC

Besleme gerilimi

akım / AC'de / anma değeri	20 A
işletim gerilimi / anma değeri	
• minimum	230 V
• maksimum	230 V

Koruma sınıfı

IP koruma türü	IP20
----------------	------

Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	1,7 W
--	-------

Ana devre

işletim akımı / anma değeri	20 A
-----------------------------	------

Kontrol akımı

kontrol besleme gerilimi	
• anma değeri	24 V
• anma değeri / maksimum	24 V
• DC'de / anma değeri	24 V

Ürün Detayı

ürün bileşeni / manüel anahtarlama için sürgü	Evet
ürün ilavesi / takılabilir / ilave tertibatlar	Evet

Numara

açıcı sayısı	0
kapayıcı sayısı	2

Mekanik Tasarım

yükseklik	90 mm
genişlik	17,5 mm
derinlik	71 mm
montaj derinliği	64 mm
en birimi sayısı	1
net ağırlık	150 g

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	Q
• IEC 81346-2:2009 uyarınca	Q

General Product Approval

Declaration of Conformity



CCC



UL

[Miscellaneous](#)



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5TT5000-8>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5TT5000-8>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5000-8

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





