

INSTA contactor with 4 NC contacts Contact for 230 V AC, 400V 40A
Control AC/24 V DC



Versiyon

ürün marka adı	SETRON
ürün tanımı	Insta kontaktörler
gerilim türü / işletim gerilimi	AC
gerilim türü / çalıştırmak için	AC/DC

Besleme gerilimi

akım / AC'de / anma değeri	40 A
işletim gerilimi / anma değeri	
• minimum	400 V
• maksimum	400 V

Koruma sınıfı

IP koruma türü	IP20
----------------	------

Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	4 W
--	-----

Ana devre

işletim akımı / anma değeri	40 A
-----------------------------	------

Kontrol akımı

kontrol besleme gerilimi

- anma değeri 24 V
- anma değeri / maksimum 24 V
- DC'de / anma değeri 24 V

Ürün Detayı

ürün bileşeni / manüel anahtarlama için sürgü Hayır

ürün ilavesi / takılabilir / ilave tertibatlar Evet

Numara

açıcı sayısı 4

kapayıcı sayısı 0

Mekanik Tasarım

yükseklik 90 mm

genişlik 53,5 mm

derinlik 71 mm

montaj derinliği 64 mm

en birimi sayısı 3

net ağırlık 150 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca Q
- IEC 81346-2:2009 uyarınca Q

General Product Approval

Declaration of Conformity



CCC



UL

[Miscellaneous](#)



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5TT5043-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5TT5043-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5043-2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





