

INSTA contactor with 2 NO contacts and 2 NC Contact for 230 V AC,
400V 63A Control AC/24 V DC



Versiyon

ürün marka adı	SETRON
ürün tanımı	Insta kontaktörler
gerilim türü / işletim gerilimi	AC
gerilim türü / çalıştırmak için	AC/DC

Besleme gerilimi

akım / AC'de / anma değeri	63 A
işletim gerilimi / anma değeri	
• minimum	400 V
• maksimum	400 V

Koruma sınıfı

IP koruma türü	IP20
----------------	------

Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	8 W
--	-----

Ana devre

işletim akımı / anma değeri	63 A
-----------------------------	------

Kontrol akımı

kontrol besleme gerilimi

- anma değeri

24 V

Ürün Detayı

ürün bileşeni / manüel anahtarlama için sürgü

Hayır

ürün ilavesi / takılabilir / ilave tertibatlar

Evet

Numara

açıcı sayısı

2

kapayıcı sayısı

2

Mekanik Tasarım

yükseklik

90 mm

genişlik

53,5 mm

derinlik

71 mm

montaj derinliği

64 mm

en birimi sayısı

3

net ağırlık

150 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

Q

Q

General Product Approval

Declaration of Conformity



[Miscellaneous](#)



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5TT5052-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5TT5052-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5052-2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





