

Class J fuse link 300 A 600 V time-lag, respect national installation rules!



Versiyon

ürün marka adı	SETRON
ürün tanımı	Silindirik sigorta
ürün modeli	Ölçüm cihazı kontaklı

Genel teknik veriler

sigorta soketinin çalışma sınıfı	taşıyıcı
sigorta soketinin büyüklüğü	Sınıf J
gerilim türü	AC
akım / AC'de / anma değeri	300 A
işletim gerilimi / anma değeri	600 V

Ana devre

işletim akımı / nominal değer	300 A
-------------------------------	-------

Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	720 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

General Product Approval



CSA



UL

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW4550-2HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW4550-2HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4550-2HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



