

ALPHA 160, wall-mounted cabinet, Surface mounting, with distribution board panel, IP43, Protection class 2, H: 500 mm, W: 300 mm, T: 140 mm, RAL 9016



Versiyon

| | |
|----------------|---------------------------------------|
| ürün marka adı | ALPHA 160 |
| ürün tanımı | Duvar dolabı |
| ürün modeli | Sıva üstü, dağıtıcı alan ile birlikte |
| yüzey işleme | toz kaplamalı |

Koruma sınıfı

| | |
|---|-------|
| IP koruma türü | IP43 |
| etkileşim uygunluğu / flaş koruması | Evet |
| kullanma uygunluğu / harici kullanım için | Hayır |

Görünüm

| | |
|---|----------|
| RAL renk numarası | RAL 9016 |
| ürün bileşeni | |
| • kablo girişi | Evet |
| • montaj plakası | Hayır |
| ürün ilavesi / opsiyonel / yan yana seri bağlantı | Hayır |
| DIN rayları sayısı | 3 |

Mekanik Tasarım

| | |
|-----------|--------|
| yükseklik | 500 mm |
|-----------|--------|

| | |
|---|---------|
| genişlik | 300 mm |
| derinlik | 140 mm |
| montaj derinliği | 140 mm |
| en birimi sayısı / DIN montaj rayı sayısı | 36 |
| net ağırlık | 6,56 kg |
| malzeme / mahfaza | Çelik |



Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

U

UC

| General Product Approval | Declaration of Conformity | Test Certificates |
|--|---|---|
|  Miscellaneous |  EG-Konf. | Miscellaneous Type Test Certificates/Test Report Special Test Certificate |

other

[Miscellaneous](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=8GK1052-1KK11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/8GK1052-1KK11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1052-1KK11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

