

SETRON, cylindrical fuse link, Class CC, 6 A, quick, Un AC: 600 V, respect national installation rules!



Versiyon

| | |
|----------------|--------------------|
| ürün marka adı | SETRON |
| ürün tanımı | Silindirik sigorta |

Genel teknik veriler

| | |
|----------------------------------|----------|
| sigorta soketinin çalışma sınıfı | hızlı |
| sigorta soketinin büyüklüğü | Sınıf CC |
| gerilim türü | AC |
| akım / AC'de / anma değeri | 6 A |
| işletim gerilimi / anma değeri | 600 V |

Ana devre

| | |
|-------------------------------|-----|
| işletim akımı / nominal değer | 6 A |
|-------------------------------|-----|

Ürün Detayı

| | |
|---------------------------------|------------------------------|
| ürün bileşeni / darbe dedektörü | Hayır |
| montaj pozisyonu | isteğe bağlı, tercihen dikey |
| net ağırlık | 7 g |

Sertifikalar

| | |
|------------------|--|
| referans işareti | |
|------------------|--|

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

General Product Approval

Declaration of Conformity



CSA

UL

EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW2060-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW2060-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW2060-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

