

SETRON, cylindrical fuse link, Class CC, 4 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



Versiyon

ürün marka adı	SETRON
ürün tanımı	Silindirik sigorta

Genel teknik veriler

sigorta soketinin çalışma sınıfı	taşıyıcı, elektrik sınırlamalı
sigorta soketinin büyüklüğü	Sınıf CC
gerilim türü	AC
akım / AC'de / anma değeri	4 A
işletim gerilimi / anma değeri	600 V

Ana devre

işletim akımı / nominal değer	4 A
-------------------------------	-----

Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	1 g

Sertifikalar

referans işareti	
------------------	--

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

General Product Approval

Declaration of Conformity



CSA

UL

EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW3040-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW3040-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW3040-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

