

SENTRON, cylindrical fuse holder, 10 x 38 mm, 2-pole, In: 25 A, Ue DC: 1000 V, LED Signal detector, for photovoltaic application



### Versiyon

ürün marka adı	SENTRON
ürün tanımı	Silindirik sigorta tutucusu
ürün modeli	Fotovoltaik uygulama için LED sinyal dedektörü

### Genel teknik veriler

kutup sayısı	2
sigorta elemanı ebadı	10x38 mm

### Besleme gerilimi

akım / AC'de / anma değeri	25 A
işletim gerilimi	
• DC'de / anma değeri	1 000 V
IP koruma türü	IP20

### Mekanik Tasarım

yükseklik	85 mm
genişlik	36 mm
derinlik	65 mm
net ağırlık	123 g

## Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

Declaration of Con-  
formity

other



[Miscellaneous](#)

## Diğer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW7024-4>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW7024-4>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7024-4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024-4)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

