

SITOR cylindrical fuse link, 22x127 mm, 40 A, gR, Un AC: 1500 V,
Un DC: 1000 V



Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR silindirik sigorta buşonu

Genel teknik veriler

sigorta soketinin çalışma sınıfı	gR
sigorta soketinin büyüklüğü	22x127 mm
gerilim türü	AC
akım / AC'de / anma değeri	40 A
besleme gerilimi / DC'de	1 000 V
işletim gerilimi / anma değeri	1 500 V

Ana devre

işletim akımı / nominal değer	40 A
-------------------------------	------

Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
montaj pozisyonu	isteğe bağlı, tercihen dikey
net ağırlık	96 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

[Miscellaneous](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NC2340-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NC2340-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2340-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



