

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 300 mm, T: 250 mm, RAL 7035



### Versiyon

ürün marka adı	ALPHA 630
ürün tanımı	Ayaklı pano
ürün modeli	açık yan duvar ile birlikte
yüzey işleme	toz kaplamalı

### Koruma sınıfı

IP koruma türü	IP55
etkileşim uygunluğu / flaş koruması	Evet
kullanma uygunluğu / harici kullanım için	Hayır

### Görünüm

RAL renk numarası	RAL 7035
ürün bileşeni	
• kablo girişi	Evet
• montaj plakası	Hayır
ürün ilavesi / opsiyonel / yan yana seri bağlantı	Evet

### Mekanik Tasarım

yükseklik	1 950 mm
genişlik	300 mm

derinlik	250 mm
montaj derinliđi	250 mm
net ađırlık	26,5 kg
malzeme / mahfaza	Çelik

## Sertifikalar

### referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

### other

[Miscellaneous](#)

## Diđer bilgiler

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=8GK1323-8KP13>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/8GK1323-8KP13>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KP13](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP13)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



