

DIAZED fuse base Size DII Molded plastic, 3-pole touch-protected (BGV A2) Access: Double function terminal Outgoing feeder: Box terminal 25A 500 V AC



Versiyon

ürün marka adı	SETRON
ürün tanımı	Sigorta sistemi DIAZED
ürün modeli	DIAZED yuvası
sigorta yuvası modeli	Ek master

Genel teknik veriler

kutup sayısı	3
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	DII

Besleme gerilimi

akım / AC'de / anma değeri	25 A
besleme gerilimi / AC'de / anma değeri	500 V

Ürün Detayı

ürün bileşeni / kapak	Evet
-----------------------	------

Mekanik Tasarım

yükseklik	120 mm
genişlik	80 mm
derinlik	55 mm

net ağırlık	454 g
malzeme / mahfaza	plastik

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

Declaration of Conformity



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SF5068>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SF5068>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF5068

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



