

SR60 base DIAZED DIII 3-pole 690 V AC 500 V DC for Adapter screw for 5/10 mm busbar thickness with clamp-type terminals



Figure similar

Versiyon	
ürün marka adı	SETRON
ürün tanımı	Sigorta sistemi DIAZED
ürün modeli	SR60 KAİDE
sigorta yuvası modeli	Ek master

Genel teknik veriler	
kutup sayısı	3
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	DIII

Besleme gerilimi	
akım / AC'de / anma değeri	63 A
besleme gerilimi / AC'de / anma değeri	690 V

Ürün Detayı	
ürün bileşeni / kapak	Hayır

Mekanik Tasarım	
yükseklik	200 mm
genişlik	57 mm

derinlik	43,5 mm
net ağırlık	290 g
malzeme / mahfaza	diğer

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

Test Certificates

[Type Test Certificates/Test Report](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SF6215>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SF6215>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF6215

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

