

NEOZED, fuse base, D03, 1-pole, 100 A, Un AC: 400 V, Un DC: 250 V, without cover



Figure similar

Versiyon	
ürün marka adı	NEOZED
ürün tanımı	Emniyet soketi
ürün modeli	NEOZED montaj emniyet kaidesi
ürün varyasyonu	Kapaksız
Genel teknik veriler	
kutup sayısı	1
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	D03
Besleme gerilimi	
işletim gerilimi / anma değeri	400 V
Dağıtım	
Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	2,5 W
Ana devre	
işletim akımı / anma değeri	100 A

Ürün Detayı

ürün bileşeni / kapak Hayır

Mekanik Tasarım

yükseklik	86 mm
genişlik	44,9 mm
derinlik	44 mm
sabitleme türü	DIN rayı
net ağırlık	204 g
malzeme / D emniyet duyusu	Porselen

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F
F

**Declaration of Con-
formity**

Test Certificates



EG-Konf.

[Special Test Certificate](#)

[Type Test
Certificates/Test Report](#)

[Miscellaneous](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG1812>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG1812>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1812

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

