

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V



Versiyon

ürün marka adı	NEOZED
ürün tanımı	Emniyet soketi
ürün modeli	NEOZED montaj emniyet kaidesi

Genel teknik veriler

kutup sayısı	3
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	D02

Besleme gerilimi

işletim gerilimi / anma değeri	400 V
--------------------------------	-------

Dağıtma

Güç kaybı [W] / akım anma değeri / AC'de / sıcak işletim durumunda / kutup başına	3 W
---	-----

Ana devre

işletim akımı / anma değeri	63 A
-----------------------------	------

Ürün Detayı

ürün bileşeni / kapak	Evet
-----------------------	------

Mekanik Tasarım

yükseklik	59 mm
genişlik	80,8 mm
derinlik	41 mm
sabitlenme türü	DIN rayı
net ağırlık	260 g
malzeme / D emniyet duyusu	Porselen

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

Declaration of Conformity



VDE



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG5653>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG5653>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG5653

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

