

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V, for Busbar system 8US 60 mm



Versiyon

ürün marka adı	NEOZED
ürün tanımı	Emniyet soketi
ürün modeli	NEOZED üst kaide
ürün varyasyonu	8US 60 mm elektrik dağıtım rayı sistemi için

Genel teknik veriler

kutup sayısı	3
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	D02

Besleme gerilimi

işletim gerilimi / anma değeri	400 V
--------------------------------	-------

Dağıtım

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	3 W
--	-----

Ana devre

işletim akımı / anma değeri	63 A
-----------------------------	------

Ürün Detayı

ürün bileşeni / kapak	Evet
-----------------------	------

Mekanik Tasarım

yükseklik	200 mm
genişlik	36 mm
derinlik	43 mm
sabitlenme türü	Ray sistemi
net ağırlık	165 g
malzeme / D emniyet duygusu	Plastik

Sertifikalar

referans işareti	
• DIN EN 61346-2 uyarınca	F
• IEC 81346-2:2009 uyarınca	F

Declaration of Conformity



EG-Konf.

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SG6207>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SG6207>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG6207

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

