

shunt release 110-415 V AC, for miniature circuit breaker 5SL4, 5SY, 5SP, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Versiyon

ürün marka adı	SENTRON
ürün tanımı	Çalışma akımı tetikleyici
ürün modeli	takılabilir
elektrikli işletim süresi (işletim çevrimleri) / tipik	20 000

Besleme gerilimi

işletim gerilimi	
• anma değeri	230 V
IP koruma türü	IP20

Ürün Detayı

ürün ilavesi	Çalışma akımı tetikleyici
--------------	---------------------------

Numara

hata sinyali anahtarı sayısı	0
açıcı sayısı	0
kapayıcı sayısı	2
değiştirici sayısı	0

Bağlantılar

bağlanabilir kablo kesiti	0,5 ... 2,5 mm ²
sıkma torku / vida bağlantısında	0,5 N·m
bağlanabilir iletken kesit türü / AWG hatlarında	24 ... 12

Mekanik Tasarım

yükseklik	90 mm
genişlik	18 mm
derinlik	70 mm
net ağırlık	100 g
• işletim sırasında	-25 ... +55 °C
• depolama sırasında	-40 ... +75 °C

Sertifikalar

Declaration of Con- formity	other	Railway
--	--------------	----------------



EG-Konf.

[Environmental Confirma-
tions](#)

[Miscellaneous](#)

[Vibration and Shock](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5ST3030>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5ST3030>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3030

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





