

shunt release 110-480 V AC for miniature circuit breaker according to UL 489



Versiyon

ürün marka adı	SETRON
ürün tanımı	Çalışma akımı tetikleyici
ürün modeli	takılabilir
elektrikli işletim süresi (işletim çevrimleri) / tipik	12 000

Besleme gerilimi

işletim gerilimi	
• anma değeri	480 V
IP koruma türü	IP20

Ürün Detayı

ürün ilavesi	Çalışma akımı tetikleyici
--------------	---------------------------

Numara

hata sinyali anahtarı sayısı	0
açıcı sayısı	0
kapayıcı sayısı	0
değiştirici sayısı	0

Bağlantılar

bağlanabilir kablo kesiti	0,5 ... 2,5 mm ²
sıkma torku / vida bağlantısında	0,8 N·m
bağlanabilir iletken kesit türü / AWG hatlarında	24 ... 12

Mekanik Tasarım

yükseklik	110 mm
genişlik	18 mm
derinlik	70 mm
net ağırlık	117 g

Sertifikalar

General Product Approval

Declaration of Conformity



Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5ST3030-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5ST3030-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3030-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



