

DIAZED fuse base size DII Molded plastic, 1-pole touch-protected (BGV A2) Access: Double function terminal Outgoing feeder: Box terminal 25A 500 V AC



### Versiyon

ürün marka adı	SETRON
ürün tanımı	Sigorta sistemi DIAZED
ürün modeli	DIAZED yuvası
sigorta yuvası modeli	Ek master

### Genel teknik veriler

kutup sayısı	1
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	DII

### Besleme gerilimi

akım / AC'de / anma değeri	25 A
besleme gerilimi / AC'de / anma değeri	500 V

### Ürün Detayı

ürün bileşeni / kapak	Evet
-----------------------	------

### Mekanik Tasarım

yükseklik	40 mm
genişlik	80 mm
derinlik	55 mm

net ağırlık	154 g
malzeme / mahfaza	plastik

## Sertifikalar

### referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

## Declaration of Conformity



EG-Konf.

## Diğer bilgiler

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SF1060>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SF1060>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SF1060](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1060)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



