

DIAZED base DIII 63 A 690 V AC 500 V DC Clamp terminal/saddle terminal



Figure similar

Versiyon

ürün marka adı	SETRON
ürün tanımı	Sigorta sistemi DIAZED
ürün modeli	DIAZED yuvası
sigorta yuvası modeli	Ek master

Genel teknik veriler

kutup sayısı	1
sigorta sistemi ebadı / DIN EN 60269-1 uyarınca	DIII

Besleme gerilimi

akım / AC'de / anma değeri	63 A
besleme gerilimi / AC'de / anma değeri	690 V

Ürün Detayı

ürün bileşeni / kapak	Hayır
-----------------------	-------

Mekanik Tasarım

yükseklik	80 mm
genişlik	46 mm

derinlik	47 mm
net ağırlık	167,5 g
malzeme / mahfaza	Porselen

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=5SF1205>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/5SF1205>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1205

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



