

SENTRON, cylindrical fuse link, 14x51 mm, 16 A, gG, Un AC: 690 V



## Versiyon

ürün marka adı	SENTRON
ürün tanımı	Silindirik sigorta

## Genel teknik veriler

sigorta soketinin çalışma sınıfı	gG
sigorta soketinin büyüklüğü	14x51 mm
gerilim türü	AC
akım / AC'de / anma değeri	16 A
besleme gerilimi / DC'de	250 V
işletim gerilimi / anma değeri	690 V

## Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	2,1 W
--	-------

## Ana devre

işletim akımı / nominal değer	16 A
-------------------------------	------

## Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
montaj pozisyonu	isteğe bağlı, tercihen dikey

net ağırlık

21 g

## Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

## Diğer bilgiler

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NW6105-1>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/tr/ps/3NW6105-1>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW6105-1](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6105-1)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

