

SITOR cylindrical fuse link, 14x51 mm, 10 A, aR, Un AC: 690 V, Un DC: 800 V, DC according to UL



Versiyon

ürün marka adı	SETRON
ürün tanımı	SITOR silindirik sigorta buşonu
ürün modeli	DC UL uyarınca

Genel teknik veriler

sigorta soketinin çalışma sınıfı	aR
sigorta soketinin büyüklüğü	14x51 mm
gerilim türü	AC
akım / AC'de / anma değeri	10 A
besleme gerilimi / DC'de	700 V
işletim gerilimi / anma değeri	690 V

Dağıtma

Güç kaybı [W] / akım anma değerinde / AC'de / sıcak işletim durumunda / kutup başına	4 W
--	-----

Ana devre

işletim akımı / nominal değer	10 A
-------------------------------	------

Ürün Detayı

ürün bileşeni / darbe dedektörü	Hayır
---------------------------------	-------

montaj pozisyonu	isteğe bağı, tercihen dikey
net ağırlık	19 g

Sertifikalar

referans işareti

- DIN EN 61346-2 uyarınca
- IEC 81346-2:2009 uyarınca

F

F

General Product Approval

Declaration of Conformity



[Miscellaneous](#)



Diğer bilgiler

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/tr/tr/Catalog/product?mlfb=3NC1410>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/tr/ps/3NC1410>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1410

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



