



# Vita TV-L2BT Headset



Volume amplification  
**+110dB**



Tone enhancement



Bluetooth multi point



NFC for easy pairing



Rechargeable battery



## GB TV and mobile headset

- ▶ Regulable and graduable earphones
- ▶ 110dB amplification
- ▶ Tone enhancement
- ▶ NFC for Easy Pairing
- ▶ Bluetooth multipoint connection for Handsfree / TV / Music
- ▶ Ambient amplification
- ▶ Charging desk and direct charging for mobile use
- ▶ Built-in rechargeable battery

## FR Casques d'écoute pour télé et mobiles

- ▶ Ecouteurs réglables
- ▶ Amplification jusqu'à 110 db
- ▶ Réglage de la tonalité
- ▶ NFC appairage facile et sécurisé
- ▶ Main libre par bluetooth Multi point (TV, mobile, tablette...)
- ▶ Possibilité d'amplification du son ambiante
- ▶ Station pour charge directe, mobilité en plus
- ▶ Batterie rechargeable intégrée

## IT Auricolare per TV e cellulari

- ▶ Auricolari regolabili e graduabile
- ▶ Amplificazione 110dB
- ▶ Valorizzazione tone
- ▶ NFC per l'accoppiamento facile
- ▶ Multipunto Bluetooth per viva voce / TV / Musica
- ▶ Amplificazione ambientale
- ▶ Carica scrivania e ricarica diretta per l'utilizzo mobile
- ▶ Batteria ricaricabile integrata

## DE Kopfhörer für TV und Mobil

- ▶ Regulierbare und einstellbare Ohrhörer
- ▶ 110dB Verstärkung
- ▶ Tonregelung
- ▶ NFC für einfaches Pairing
- ▶ Bluetooth Multipoint-Verbindung für Freisprechen / TV / Musik
- ▶ Umgebungsverstärkung
- ▶ Ladestation und direkte Aufladung für den mobilen Einsatz
- ▶ Integrierter Akku



Earphones regulable and graduable


Handsfree / TV / Music

Ambient amplification

Optical and analog plug

Charging and docking station

Product launch date:	May 2017
Unit size:	231 x 120 x 28 mm
Product weight (with package):	ca. ?g
Package size:	???? mm
Package content:	1x headset, 1x charger / transmitter, 1x power adapter, 1x Earplugs, 3x Cable, 1x user manual
Adapters / Plugs:	Europe
Product menu languages:	-
Giftbox languages:	GB/FR/IT/DE/NL/ES/PT/SWE/TR/PL/RU
Userguide languages:	DE/GB/FR/IT/ES/PT/NL





## Vita TV-L2BT Headset



### Bluetooth Transmitter:

- ▶ Bluetooth V4.0
- ▶ Power supply voltage 5V 550 mA
- ▶ Power adapter
- ▶ Docking charging compartment for headphones
- ▶ Size: 110(W)x102(D)x39(H)mm

### Bluetooth Chin Headset:

- ▶ Bluetooth V4.0
- ▶ NFC
- ▶ Tone enhancement button
- ▶ Left and right ear volume adjustment
- ▶ Mic button for sound amplification
- ▶ Phone/Play/Pause button
- ▶ Built-in rechargeable battery
- ▶ Direct line-in (Optional)
- ▶ Speaker size: 15mm
- ▶ Impedance: 16 ohm
- ▶ Freq. response: 350Hz - 8KHz
- ▶ THD: < 1%
- ▶ S/N ratio : 75dB
- ▶ Charging time: 3 hrs
- ▶ Operation time: 9 hrs
- ▶ Operation distance: 10M
- ▶ Size: 120(W)x28(D)x231(H)mm
- ▶ Easy-to-deck charger with big buttons design

