

# VS-EC-MSDB SH SCO

Obj.č.: 1440711


<http://eshop.phoenixcontact.cz/phoenix/treeViewClick.do?UID=1440711>

Vestavná zástrčka senzoru/aktoru, Mini-B USB, M 12-SPEEDCON, s  
přímým pájeným spojem

## Údaje

|                      |                                                                                                      |
|----------------------|------------------------------------------------------------------------------------------------------|
| EAN                  | <br>4 046356 554053 |
| Balení               | 1 ks                                                                                                 |
| Celní tarif          | 85366990                                                                                             |
| Váha brutto v kusech | 0,22222 kg                                                                                           |
| Informace v katalogu | Strana 205 (CAT-2-2013)                                                                              |

## Poznámky k produktu

WEEE/RoHS-compliant since:  
01.01.2009



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technické údaje

### Mechanické parametry

|                            |                                     |
|----------------------------|-------------------------------------|
| Počet pólů                 | 4                                   |
| stíněno                    | ano                                 |
| Cykly zapojení             | ≥ 100                               |
| Způsob připojení           | Pájecí trny                         |
| Teplota prostředí (provoz) | -25 °C ... 85 °C (Zástrčka/zásuvka) |


#### Údaje o materiálu

|                              |                            |
|------------------------------|----------------------------|
| Třída hořlavosti podle UL 94 | V0                         |
| Materiál kontakt             | Cu slitina                 |
| Materiál povrch kontaktu     | Zlato přes nikl            |
| Materiál šroubového uzávěru  | Zinkový odlitek, niklovaný |
| Druh ochrany                 | IP67                       |

#### Elektrické parametry

|                                |                                |
|--------------------------------|--------------------------------|
| Vlastnosti přenosu (kategorie) | CAT7, pro USB 2.0 (480 MBit/s) |
|--------------------------------|--------------------------------|

#### Certifikáty/Osvědčení



Aprobace

GOST

Vyžádané aprobace:

Aprobace z:

#### Příslušenství

| Informace | Popis | Popis výrobku |
|-----------|-------|---------------|
|-----------|-------|---------------|

#### Ochranné a uzavírací prvky

|         |                               |                                                                                                              |
|---------|-------------------------------|--------------------------------------------------------------------------------------------------------------|
| 1456187 | PROT-M12 FS-PA-CHAIN-EYE-DM12 | Uzavírací krytka M12 z plastu s upevňovací páskou, pro neosazené zástrčky M12 s připevňovacími oušky 12,0 mm |
|---------|-------------------------------|--------------------------------------------------------------------------------------------------------------|

Vrtací schéma/geometrie pájecí desky

A diagram of a 5-pin connector, enclosed in a circle. The pins are numbered 1 to 5 from right to left. The connector is shown in a perspective view, with a top row of five pins and a bottom row of five pins. The top row is labeled 1, 2, 3, 4, 5 from right to left. The bottom row is unlabeled.

**Adresa**

PHOENIX CONTACT, s.r.o.  
Dornych 47  
617 00 Brno, Czech Republic  
Telefon +420 542 213 401  
Fax +420 542 213 701  
<http://www.phoenixcontact.cz>



© 2013 Phoenix Contact  
Technické změny vyhrazeny.