



Pomocný kontakt pro PLS., PKDM, PFHM-2p, 1S+1R, 0.5HP

Typ Z-AHK
Catalog No. 248433

Dodavatelský program

Základní funkce			příslušenství pro proudový chránič s nadproudovou ochranou příslušenství pro proudový chránič příslušenství pro instalační jistič
Základní funkční příslušenství			Pomocné kontakty
Použití			Spínací přístroje pro průmyslové použití a účelové stavby
Sortiment			Příslušenství
Side mounting			for fitting on left to: LS, FI/LS
Značka zapojení			

Technická data

Ověření návrhu podle ČSN EN 61439

Technické údaje pro ověření konstrukce			
Provozní teplota okolí min.		°C	-5
Provozní teplota okolí max.		°C	40

Technická data podle ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)			
Elektrotechnika, automatizační technika a technika řízení procesu / Elektroinstalacní zařízení, přístroj / Komponenta ochranného snímace / Pomocný kontakt, signalizační kontakt (ecl@ss10.0.1-27-14-35-02 [AKE327013])			
Device fitting			Universal
Additional equipment			Auxiliary switch
Attached at delivery			No
Assembly width (TE)			0.5
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			1
Number of contacts as change-over contact			0
Number of fault-signal switches			0
Rated switch current		A	3
Rated voltage		V	230
Voltage type for actuating			AC
With auto test for earth leakage function			No
Suitable for max. number of poles main contact unit (total)			2
Suitable for max. current main contact unit		A	4

