



TYPE	PRIMÄRSTROM(A)	NENNLEISTUNG(VA)
ENT.B	5-10-15	5-10-15
ENT.B	20-25-30-40	5
	50-60-75-80	10
	100-125-150	15



ENT.30	30-40-50-75-100-150	5
ENT.30	200	5
ENT.30	250-300	5-10



ENT.40	400-500-600	10
	400	15
	600	15

ENT.60	750-800	10
ENT.60	1000-1200-1250	10
	1000	15
ENT.100	1000-1250	10
ENT.100	1500-1600	15



TEILBARE STROMWANDLER


ENS.AYS 23	100	1,25
	300	3,75

ENS.AYS 58	500	5
------------	-----	---

ENS.AYS 812	400	1,5
	500-600-800	2,5
	1000	5

ENS.AYS 816	1200	10
	1500-1600-2000	15
	2500-3000	15
	4000	30



STROMWANDLER FÜR NIEDERSPANNUNG	TYP	EIGENSCHAFTEN	FÜR ENTES GERÄTE	
			120 A	210 A
 <p>(Für ENTES Digitalmessgeräte)</p>	CT-25	Verhältnis : 1/2500, Klasse:1 Innendurchmesser : 17.8mm Aussendurchmesser : 47mm	MPR-53 MPR-53S EPR-04 EPR-04S EPM-04 EPM-04C EPM-04CS EPM-06 EPM-06C EPM-06CS	EPM-4A EPM-4C EPM-4D EPM-4P
	CT-80D (nur für ES-80L)	Verhältnis : 1/2500, Klasse:1 Innendurchmesser : 19mm Aussendurchmesser : 47.5mm		

