

Wire end sleeve set

Set d'embouts

Adereindhulzenet

Aderendhülsen-Set

Nr. 73 70 30

2700 Stück

Isoliert/Isolated/Isolé/Geïsoleerd

0,5 x 8 mm, 105° C/ 300V · 0,75 x 8 mm, 105°C/ 300V ·
 1,0 x 8 mm, 105° C/ 300V · 1,5 x 8 mm, 105°C/ 300V ·
 2,5 x 8 mm, 105° C/ 300V · 4,0 x 9 mm, 105°C/ 300V ·
 6,0 x 12 mm, 105° C/ 300V · 10 x 12 mm, 105°C/ 300V

Unisoliert/Non-Isolated/Non-Isolé/Niet-geïsoleerd

0,5 x 8 mm · 0,75 x 8 mm · 1,0 x 6 mm · 1,5 x 8 mm



Conrad Electronic SE, Hirschau

www.conrad.com


Aderendhülsen-Set 2700 Stück

Wire end sleeve set 2700 pieces

Set d'embouts 2700 pièces


Adereindhulzenet 2700 stuks


Inhalt/ Content/ Contenu/ Inhoud:
Isoliert/Isolated/Isolé/Geïsoleerd

0,5 x 8 mm, 105° C/ 300V orange/orange/orange/orange
 0,75 x 8 mm, 105° C/ 300V weiss/white/blanc/wit
 1,0 x 8 mm, 105° C/ 300V gelb/yellow/jaune/geel
 1,5 x 8 mm, 105° C/ 300V rot/red/rouge/rood
 2,5 x 8 mm, 105° C/ 300V blau/blue/bleu/blauw
 4,0 x 9 mm, 105° C/ 300V grau/grey/gris/grijs
 6,0 x 12 mm, 105° C/ 300V schwarz/noir/zwart
 10 x 12 mm, 105° C/ 300V matt-transparent/
 mat-transparent/mat transparent/transparante mat

Unisoliert/Non-Isolated/Non-Isolé/Niet-geïsoleerd

0,5 x 8 mm
 0,75 x 8 mm
 1,0 x 6 mm
 1,5 x 8 mm



SPECIFICATION

MATERIAL : Poly Propylene (PP)
 COLOR : Transparent
 TOLERANCE : ± 1mm

DATE	REVISION	APPROVAL BY	DIMENSION	mm	MODEL No	EKB-206
			DRAW BY	Michael	NAME	PLASTIC BOX
			APPROVAL BY	Rikki		
			DATE	30-09-05		

737030

ADERENDHÜLSEN-SET 2700 STÜCK

Die Maße der geschlossenen Box betragen über alles:
Breite ca. 200mm; Höhe ca. 38mm; Tiefe ca. 145mm