

















MONTAGEANLEITUNG

-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONE DELL'ASSEMBLEA
-  INSTRUCCIÓN DE ASAMBLEA
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING

-  MONTAJ TALIMATI
-  ASENNUSOHJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  SZERELÉSI ÚTMUTATÓ
-  INSTRUCTIUNI DE MONTAJ



Modell-Nr.

70290

ART.-NR. FRONT KORPUS

70291  Silber

70292  Silber

70294  Silber

70297  Silber

70296  

Friedrich Küpper GmbH
Friedrich-Küpper-Weg
54570 Berlingen
Deutschland

Telefon +49 (0) 65 91 - 95 42 0
Telefax +49 (0) 65 91 - 95 42 17
E-Mail info@friedrich-kuepper-gmbh.de
Internet www.friedrich-kuepper-gmbh.de

EINZELTEILE / PIECES

B

1x

910 mm x 450 mm



I

1x

1770 mm x 70 mm



D

1x

905 mm x 405 mm



K

1x

910 mm x 100 mm



E

1x

1770 mm x 430 mm



L

1x

1665 mm x 450 mm



F

1x

1770 mm x 430 mm



M

1x

1665 mm x 458 mm



G

2x

1770 mm x 385 mm























N

4x






900 mm x 380 mm



BEUTELINHALT / BAG CONTENT



 4x M6x16 mm	 16x M6x12 mm	 4x M6x16 mm	 24x ø6,4 mm	 24x M6	 4x M4 x 10 mm
 4x M4	 4x ø4,3 mm	 4x	 4x 5x5	 4x 5x15	 4x
 4x	 4x	 2x	 1x	 1x	 1x
 1x	 1x	 1x			

BENÖTIGTES WERKZEUG / NEEDED TOOLS


 1 PH 1 x 100 PH 2 x 100 Schlitz 6,5 x 150	 2 SW 7 SW 10	 5
 6 5 mm	 9	

1.

① 
Schlitz 6,5 x 150



2.



3.



4x M6



4x M6 x 12



4x 6,4 MM



2x SW 10

4.




5.



6.



7.



8.

4x M6 x 12



9.

4x M6

4x 6,4 MM

②  SW 10



10.



11.

4x M6 4x M6x16 4x 6,4 mm 2x

⑥



12.


4x



13.

2x

① PH2x100




14.

2x



15.

4x M6 4x M6x16 4x 6,4 mm 2x ① PH2x100 ② SW10



16.



17.

4x M6 x 12 4x 6,4 MM



18.

4x M6 x 12 4x 6,4 MM



19.

8x M6

② SW 10



20.

2x 5x15

⑤



21.  2x 5x5




22.  2x 5x 15


5 



23.  2x 5x5




24.  1x




25.  1x M4  1x M4x10  1x 4,3mm  ① PH 1x100  ② SW 7



26.




27.  1x  1x M4  1x M4x10  1x 4,3mm  ① PH 1x100  ② SW 7



28.  1x



29.  1x M4  1x M4x10  1x 4,3mm  ① PH 1x100  ② SW 7




30.



31.  1x  1x M4  1x M4x10  1x 4,3mm

①  PH 1x100 ②  SW 7



32.




9



33.



34.



35.  1x




36.  1x  1x

⑨ 



37.

① 
Schlitz 6,5 x 150



38.




39.



40.



A. 



B. 



C. 



D. 



Modell-Nr.

70290