






















-  MONTAGEANLEITUNG
-  ASSEMBLY INSTRUCTION
-  DE INSTRUCTIE VAN DE ASSEMBLAGE
-  ISTRUZIONE DELL'ASSEMBLEA
-  INSTRUCCIÓN DE ASAMBLEA
-  INSTRUCTION DE MONTAGE
-  NÁVOD K MONTÁŽI
-  MONTERINGSANVISNING
-  MONTAJ TALIMATI
-  ASENNUSOHJE
-  BRUGSANVISNING
-  BRUKSANVISNING
-  UPUTE ZA MONTAŽU
-  NAVODILA ZA MONTAŽO
-  GYŰLÉS OKTATÁS
-  INSTRUCȚIUNI DE MONTAJ



## Art.-Nr. 12160



(12161, 12162, 12164, 12166, 12167)

1x		1766 x 465 mm
1x		467 x 232 mm
1x		692 x 146 mm
3x		462 x 143 mm
1x		698 x 146 mm
2x		450 x 20 mm
1x		
1x		


10x		M5 x 10
10x		5,3
10x		M5
20x		M4 x 10
20x		M4
4x		
4x		8,4
10x		M8
2x		M 8 x 16
1x		
1x		
4x		4,5 x 25





1. - 4.



4. - 6.





7. - 16.






1.



2.



M4 x 10



M4



SW 7




PH 1 x 100





2x



4x



M4 x 10

4x



M4




SW 7





PH 1 x 100

3.





4.





5.



10x



10x



10x



6.

4x



4x



4x




4x



M 8



SW 13





7.

4x




M4 x 10


4x



M4



8.




SW 7



PH 1 x 100



9.



10.



2x



M4 x 10

2x



M4



PH 1 x 100





SW 7








11.



12.





13.

1x



2x




2x

M8 x 16



M8




14.

1x





15.



16.



